High shear mixing expertise starts with Siverson

Powder/Liquid Mixers

Repeatability in powder/liquid mixing:

- Powder incorporation rates up to 30,000 lbs/hr
- Agglomerate-free product
- Consistent repeatable results
- Minimum aeration
- Improved vessel hygiene with fewer CIP requirements
- · Convenience and ease of installation and use

Laboratory Mixers

Scale-up with reproducible mixing results:

- Over 40 interchangeable mixing assemblies available
- Enables accurate scale-up and validation
- · Digital tachometer with programmable timer and amp display
- Electric rise/fall bench stand
- · Capacity from 1ml to 12 liters



Flexibility to customize your mixing process:

- Eliminate agglomerates and fish eyes
- · Create stable emulsions and suspensions
- Reduce particle size
- Rapidly dissolve solids
- Accelerate reactions
- · Process from 1 to 8,000 gallons

For more information or a free trial give us a call @ 800.204.6400

In-Line Mixers

Mix with speed and confidence:

- Ultra sanitary design for CIP and SIP cleaning
- · Create stable emulsions and suspensions
- Rapidly dissolve solids
- Interchangeable work
 - with single or multi-stage configurations
- Product cannot bypass the rotor/stator workhead
- Aeration free
- Self-pumping at throughputs from 5 to 50,000 gallons/hour



Silverson Conversion Tool App





Silverson Machines, Inc. PO Box 589 • 355 Chestnut Street • East Longmeadow, MA 01028 800.204.6400 • Fax: 413.525.5804 • www.silverson.com